

Clickeze®

CAPE COD SYSTEMS CORPORATION

Privacy Curtains

TEL. 1-888-227-8555



- Numerous colors and patterns to choose from, organized into easy to order categories
- Custom window treatments and bedspreads also available for a complete soft goods program
- Eze-Mesh™ material available in: 12" (30.48cm), 20" (50.8cm), 22" (55.8cm), 24" (60.96cm), 28" (71.12cm) and 36" (91.44cm) standard heights. #50 (1/2" hole), choose from Tusk or Snow colors. Optional Anti-microbial mesh is available.
- Curtains manufactured to accommodate many applications
- Fabrics have been tested and pass fire safety standards

Clickeze® Privacy Curtains

Suggested Specifications

PART 1 – GENERAL

1.01 SUMMARY

A. Privacy Curtain

1.02 SECTION INCLUDES

A. Curtains

1.03 REFERENCES

A. National Fire Protection Association (NFPA)

1.04 SYSTEM DESCRIPTION

A. Performance Requirements: Provide privacy curtains that conform to the following requirements of regulatory agencies and the quality control of Clickeze®, Inpro Corporation.

1. Fire Performance Characteristics: Provide curtains that conform with NFPA 701, Fire Tests for Flame and Resistant Textiles and Films.

1.05 SUBMITTALS

A. Product Data: Manufacturer's printed product data for each type of privacy curtain specified.

B. Fabric Samples: Swatch cards of fabric samples illustrating fabric color and weave.

C. Manufacturer's Care Instruction: Printed care instructions for each curtain.

1.06 DELIVERY, STORAGE AND HANDLING

A. Deliver materials in unopened factory packaging to the jobsite.

B. Inspect materials at delivery to assure that specified products have been received.

C. Store in original packaging in a climate controlled location away from direct sunlight.

1.07 PROJECT CONDITIONS

A. Environmental Requirements: Products must be installed in an interior climate controlled environment.

1.08 WARRANTY

A. Standard Clickeze® Limited Warranty against material and manufacturing defects.

PART 2 – PRODUCTS

2.01 MANUFACTURER

A. Acceptable Manufacturer Clickeze, Inpro Corporation, PO Box 406 Muskego, WI 53150 USA; Telephone: 800.222.5556, Fax: 888.715.8407, Internet address: www.inprocorp.com

B. Substitutions: Not permitted

C. Provide all privacy curtains from a single source.

2.02 MATERIALS

A. Privacy Curtain

1. Fabric: Provide 100% polyester curtains. Fabric is to be opaque, washable, flame retardant and closely woven.

2. Shield Fabric: Provide 100% polyester, impregnated and multi-coated with Aqueous based microporous polymers.

3. Enviro GT Fabrics: Provide fabrics that are 100% Eco Polyester. Eco polyester fabrics shall be free of chlorine and PBT's (persistent, bioaccumulative and/or toxic substances).

4. Open Mesh Cloth: Provide curtain heading of open weave nylon mesh material with #50 1/2" (12.7mm) holes to permit air and steam circulation. Mesh is to be flame retardant, washable and dry-cleanable.

2.03 FINISH AND COLOR

A. Cubicle Privacy Fabric: Select solid or patterned fabric from manufacturer's standard selection.

B. Open Mesh Cloth: Provide curtain heading of mesh material in a color selected from manufacturer's standard selection.

2.04 FABRICATION

A. Privacy Curtain

1. Curtain Width: Manufacture curtains of one piece, sized to 10% wider than the track length but no less than 1' (304.8mm) extra fullness. Width tolerance ±3".

2. Curtain Height: Specify height. Bottom of privacy curtains hang 12"-15" (304.8-355.6mm) above floor. Dressing room curtains hang 4"-6" (101.6m-152.4mm) above floor. Height tolerance + 2-1/2" /- 2".

3. Curtain Heading: Manufacture with or without heading of open mesh cloth, to the same width as the curtain fabric. Include 4-ounce (113.4g) nickel-plated grommets, 6" (152.4mm) on center for carriers.

4. Seams: Bottom hem shall be double-fold and 1-1/4" (31.75mm) wide. Curtains shall be seamless if possible or lock stitch seams in two rows. Turn seam edges and lock stitch. Sewing thread to be core spun polyester.

5. Sewing Options

a. Standard: Mesh bottom band sewn to fabric – exposed.

b. Hidden Mesh: Mesh bottom band hidden under hem of fabric.

c. Framing: Fabric sewing on sides of mesh and top of mesh banding (where grommets are placed). Mesh is "framed".

d. Banding: Fabric is on top of mesh banding (where grommets are placed).

e. Snaps: Ivory plastic snaps placed on mesh bottom banding and/or on side hems.

f. Snap Tape: continuous metal snap tape placed on mesh bottom and/or on side hems.

PART 3 – EXECUTION

3.01 EXAMINATION

A. Examine areas and conditions in which the cubicle tracking systems will be installed.

1. Complete all finishing operations, including painting, before beginning installation of cubicle tracking system materials.

2. Verify that surfaces and above ceiling supports are ready to receive work.

3.02 PREPARATION

A. General: Prior to installation, clean substrate to remove dust, debris and loose particles.

3.03 INSTALLATION

A. General: Locate the cubicle track as indicated on the approved detail drawing for the appropriate substrate and in compliance with the Clickeze® installation instructions.

B. Installation of Cubicle Tracking Systems:

1. Install cubicle track, secure, rigid, and true to ceiling line.

2. Slide carriers onto the track.

3. Install end cap or stop device.

4. Secure or suspend track to ceiling system. Install with mechanical fasteners or Gridclips.

5. Install curtains on carriers ensuring smooth operation.

3.04 CLEANING

A. At completion of the installation, remove any debris and clean surfaces in accordance with the Clickeze® clean-up and maintenance instructions.